

VC-AML 7-PEA - Contact insert



1607544

<https://www.phoenixcontact.com/us/products/1607544>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Contact insert, Range of articles: VARIOCON, design: VC4, color: light gray, number of positions: 7, rated voltage: 690, rated current: 63 A, Connection method: PCB connection, Connectors may only be connected/disconnected when under no load.



The figure shows the product version VC-AML 7

Commercial data

Item number	1607544
Packing unit	5 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABLACC
GTIN	4017918980405
Weight per piece (including packing)	46.86 g
Weight per piece (excluding packing)	39.904 g
Country of origin	PL

VC-AML 7-PEA - Contact insert



1607544

<https://www.phoenixcontact.com/us/products/1607544>

Technical data

Product properties

Product type	Contact insert
Product family	VARIOCON
Series	VC-M
Type	VC4
Number of positions	7
Connection profile	6+PE
Number of module slots	5

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Rated voltage (II/2)	1000 V
Rated voltage (III/2)	1000 V
Rated voltage (III/3)	690 V
	690 V
Rated voltage	690
Rated surge voltage	6 kV
Rated surge voltage (II/2)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (III/3)	8 kV
Rated surge voltage	6 kV
	63 A
	70 A
Rated current	63 A
	63 A
Nominal voltage U_N	690 V

Connection data

Connection method	PCB connection
-------------------	----------------

Dimensions

Width	35.6 mm
Height	27.1 mm
Length	75 mm

Material specifications

Color	light gray
Color of the housing part	gray
Material Housing	PA 6.6
Material Contact	E-Cu 58
Flammability rating according to UL 94	V0

VC-AML 7-PEA - Contact insert



1607544

<https://www.phoenixcontact.com/us/products/1607544>

Insulating material group	I
Contact surface material	hard-silver plated

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

VC-AML 7-PEA - Contact insert





1607544

<https://www.phoenixcontact.com/us/products/1607544>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1607544>

 cUL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	45 A	-	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	55 A	-	-

VC-AML 7-PEA - Contact insert



1607544

<https://www.phoenixcontact.com/us/products/1607544>

Classifications

ECLASS

ECLASS-13.0	27440192
ECLASS-15.0	27440192

ETIM

ETIM 10.0	EC002943
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VC-AML 7-PEA - Contact insert



1607544

<https://www.phoenixcontact.com/us/products/1607544>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com