

# RC-09P1N12Y300 - Device connector front mounting with knurled nut



1595336

<https://www.phoenixcontact.com/us/products/1595336>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting with knurled nut, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Solder cup, Flat gasket, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1595336
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFO
GTIN	4046356206112
Weight per piece (including packing)	40.06 g
Weight per piece (excluding packing)	35.489 g
Country of origin	DE

# RC-09P1N12Y300 - Device connector front mounting with knurled nut



1595336

<https://www.phoenixcontact.com/us/products/1595336>

## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	2.5 mm <sup>2</sup>
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm <sup>2</sup>
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

#### Housing

Type	Flange housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Mounting type	Front mounting/square flange (4x Ø 3.2 mm)
Degree of protection (plugged in)	IP67

# RC-09P1N12Y300 - Device connector front mounting with knurled nut



1595336

<https://www.phoenixcontact.com/us/products/1595336>

Seal for the device

Flat gasket


# RC-09P1N12Y300 - Device connector front mounting with knurled nut

1595336

<https://www.phoenixcontact.com/us/products/1595336>

## Drawings

Schematic diagram




Connector pin assignment

# RC-09P1N12Y300 - Device connector front mounting with knurled nut

1595336

<https://www.phoenixcontact.com/us/products/1595336>

Schematic diagram



Connector pin assignment


# RC-09P1N12Y300 - Device connector front mounting with knurled nut



1595336

<https://www.phoenixcontact.com/us/products/1595336>

Schematic diagram



Dimensional drawing

# RC-09P1N12Y300 - Device connector front mounting with knurled nut



1595336

<https://www.phoenixcontact.com/us/products/1595336>

## Classifications

### ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

### ETIM

ETIM 10.0	EC003569
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-09P1N12Y300 - Device connector front mounting with knurled nut



1595336

<https://www.phoenixcontact.com/us/products/1595336>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	82e55aea-9117-4073-8adb-ceb000a7af17

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)