

RC-09P1N8A1300 - Cable connector



1595380

<https://www.phoenixcontact.com/us/products/1595380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240602

The figure shows the 12-pos. product version, with standard DIN cable gland

Commercial data

Item number	1595380
Packing unit	20 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356206327
Weight per piece (including packing)	66.37 g
Weight per piece (excluding packing)	66.37 g
Country of origin	DE

RC-09P1N8A1300 - Cable connector



1595380

<https://www.phoenixcontact.com/us/products/1595380>

Technical data

Notes

Order information:	Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
--------------------	--------------------------------------------------------

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
----------------------------------------	----

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Connector

Insulating body

Note	Order information: Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

RC-09P1N8A1300 - Cable connector



1595380

<https://www.phoenixcontact.com/us/products/1595380>

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Permissible humidity (storage/transport)	50 % ... 65 %

RC-09P1N8A1300 - Cable connector



1595380

<https://www.phoenixcontact.com/us/products/1595380>

Drawings

Schematic diagram



Connector pin assignment

RC-09P1N8A1300 - Cable connector

1595380

<https://www.phoenixcontact.com/us/products/1595380>



Schematic diagram



Connector pin assignment

RC-09P1N8A1300 - Cable connector



1595380

<https://www.phoenixcontact.com/us/products/1595380>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-09P1N8A1300 - Cable connector



1595380

<https://www.phoenixcontact.com/us/products/1595380>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	13d7b09e-8a9d-4dbf-85fc-5cbc80f6e6d3

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com