

# RF-17S1N8AWB00 - Device connector front mounting



1607893

<https://www.phoenixcontact.com/us/products/1607893>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version

Device connector front mounting, application: Signal, straight, Screw locking mechanism, M23, number of positions: 17, contact connection type: Socket, Axial O-ring, shielded: yes, number of positions: 17, connection method: Crimp connection, series: RF, This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629087

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1607893       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB31          |
| Product key                          | ABRAGL        |
| GTIN                                 | 4046356174909 |
| Weight per piece (including packing) | 29.5 g        |
| Weight per piece (excluding packing) | 28.116 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

1607893

<https://www.phoenixcontact.com/us/products/1607893>

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Order information: | Order crimp contacts Ø 1 mm separately |
|--------------------|--|

### Mounting

|               |  |
|---------------|--|
| Mounting type | Front mounting/square flange (4x Ø 3.2 mm) |
|---------------|--|

### Product properties

|                     |                                   |
|---------------------|-----------------------------------|
| Product type        | Circular connectors (device side) |
| Series              | RF                                |
| Application         | Signal                            |
| Number of positions | 17                                |
| Connection profile  | 17                                |
| Shielded            | yes                               |
| Coding              | N                                 |
| Thread type         | M23                               |

### Material specifications

|                          |              |
|--------------------------|--------------|
| Material Housing         | GD-Zn        |
| Material Rotating parts  | CuZn         |
| Material Housing surface | Ni           |
| Material Insulating body | PA 6.6       |
| Material Seal            | FPM (O-ring) |

### Electrical properties

#### Contact

|                       |         |
|-----------------------|---------|
| Contact diameter      | 1 mm    |
| Nominal current $I_N$ | 8 A     |
| Nominal voltage $U_N$ | 48 V AC |
|                       | 74 V DC |
| Overvoltage category  | III     |
| Degree of pollution   | 3       |
| Rated surge voltage   | 1.5 kV  |

### Connection data

#### Conductor connection

|                         |                  |
|-------------------------|------------------|
| Connection method       | Crimp connection |
| Contact connection type | Socket           |

### Connector

|                       |          |
|-----------------------|----------|
| Type                  | straight |
| Direction of rotation | Standard |

1607893

<https://www.phoenixcontact.com/us/products/1607893>

## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP67              |
| Ambient temperature (operation) | -20 °C ... 125 °C |
| Altitude                        | 2000 m            |

Drawings

Dimensional drawing



Installation dimensions

Dimensional drawing




Dimensional drawing

1607893

<https://www.phoenixcontact.com/us/products/1607893>

Schematic diagram



Contact chamber numbering (view of plug-in side), standard socket

# RF-17S1N8AWB00 - Device connector front mounting



1607893

<https://www.phoenixcontact.com/us/products/1607893>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1607893>

|  <b>cUL Recognized</b><br>Approval ID: E153698-20090723 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 48 V                  | 1 A                   | 26                | -                           |

|  <b>UL Recognized</b><br>Approval ID: E153698-20090723 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 48 V                  | 1 A                   | 26                | -                           |

1607893

<https://www.phoenixcontact.com/us/products/1607893>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003569 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# RF-17S1N8AWB00 - Device connector front mounting



1607893

<https://www.phoenixcontact.com/us/products/1607893>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)