

RC-09P2N8C0000 - Contact insert



1595758

<https://www.phoenixcontact.com/us/products/1595758>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 8+1, contact connection type: Pin, Crimp connection, series: NC, RC, RM, TU, UC

Commercial data

Item number	1595758
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABRAFU
GTIN	4046356208093
Weight per piece (including packing)	3.88 g
Weight per piece (excluding packing)	3.88 g
Customs tariff number	85472000
Country of origin	DE

RC-09P2N8C0000 - Contact insert

1595758

<https://www.phoenixcontact.com/us/products/1595758>



Set consists of

RC-09P2N8A0000 - Contact insert

1595744

<https://www.phoenixcontact.com/us/products/1595744>



Contact insert, number of positions: 8+1, contact connection type: Pin, Crimp connection, series: NC, RC, RM, TU, UC

RC-5AP2000 - Crimp contact

1603505

<https://www.phoenixcontact.com/us/products/1603505>



Crimp contact, Pin, turned, contact diameter: 2 mm, connection cross section: 1.5 mm² ... 2.5 mm², contact material: CuZn, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241634

RC-09P2N8C0000 - Contact insert

1595758

<https://www.phoenixcontact.com/us/products/1595758>



RC-12P2000 - Crimp contact

1597862

<https://www.phoenixcontact.com/us/products/1597862>



Crimp contact, Pin, turned, contact diameter: 1 mm, connection cross section: 0.14 mm² ... 0.56 mm², contact material: CuZn, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240882

RC-09P2N8C0000 - Contact insert



1595758

<https://www.phoenixcontact.com/us/products/1595758>

Technical data

Product properties

Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	9
Connection profile	8+1
Coding	N

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
Nominal current I _N	20 A
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.14 mm ²
Max. cross section	0.56 mm ²
Nominal current I _N	8 A
Nominal voltage U _N	48 V AC
	74 V DC

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Material Insulating body	PBT
--------------------------	-----

Connector

Direction of rotation	Counter direction
-----------------------	-------------------

RC-09P2N8C0000 - Contact insert


1595758

<https://www.phoenixcontact.com/us/products/1595758>



Drawings

Schematic diagram




RC-09P2N8C0000 - Contact insert

1595758

<https://www.phoenixcontact.com/us/products/1595758>



Schematic diagram




RC-09P2N8C0000 - Contact insert



1595758

<https://www.phoenixcontact.com/us/products/1595758>

Schematic diagram



RC-09P2N8C0000 - Contact insert



1595758

<https://www.phoenixcontact.com/us/products/1595758>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com