VS-PPC-C1-RJ45-MNNA-PG9-8Q5 - RJ45 connector

1608016

https://www.phoenixcontact.com/us/products/1608016

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IDC



Push-Pull connector

RJ45 connector, RJ45, Ethernet, CAT5 (IEC 11801:2002) (1 Gbps), 8-position, connection method: IDC fast connection, material: Metal, connection cross section: AWG 26- 22, degree of protection: IP65/IP67

Commercial data

Item number	1608016
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAA
GTIN	4046356131681
Weight per piece (including packing)	70.9 g
Weight per piece (excluding packing)	67.24 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 3.01, Order No. 2252

Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage U_N	48 V
Nominal current I_N	1.75 A
Contact resistance	0.001 Ω (Wire – IDC)
	0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5

Connection data

Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid)
	26 ... 22 (flexible)
Conductor cross-section	0.13 mm² ... 0.32 mm² (solid)
	0.14 mm² ... 0.36 mm² (flexible)

Interfaces

Signal type/category	Ethernet CAT5 (IEC 11801:2002), 1 Gbps

Dimensions

Width	22 mm

Height	30 mm
Length	72 mm

Material specifications

Material	Metal
Flammability rating according to UL 94	V0
Seal material, O-ring	NBR
Seal material cable seal	TPE
Seal material	NBR
Seal material, pin connector pattern	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	NBR
Material for screw connection	CuZn

Cable/line

External cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm
Cable cross section	0.14 mm²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 250

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	-5 °C ... 45 °C

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1608016

cUL Recognized
Approval ID: E118976

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1.75 A	- 22	-

UL Recognized
Approval ID: E118976

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1.75 A	- 22	-

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	6ecc2b5f-8b5a-45ae-a6a1-6ca00e65005d

EF3.1 Climate Change

CO2e kg	1.323 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com