

VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SCRJ Push-Pull connector,
IP67

FO connectors, degree of protection: IP65/IP67, number of positions: 2, MM, material: Metal, connection method: Push-Pull, cable outlet: straight, color: silver

Commercial data

Item number	1608045
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOBA
GTIN	4046356131711
Weight per piece (including packing)	74.8 g
Weight per piece (excluding packing)	70.84 g
Customs tariff number	85367000
Country of origin	DE

VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.4 Connectors for outside environment (optical fibre) and chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Data connector (cable side)
Type	SC-RJ
Number of positions	2
Connection profile	SCRJ
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Attenuation	≥ 2 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

Connection data

Connection technology	
Connection method	Push-Pull

Dimensions

Width	22 mm
Height	30 mm
Length	62.5 mm

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Ferrule material	Copper alloy
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
O-ring material	NBR

VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Cable/line

Cable type	Plastic-coated fiber
External cable diameter	6.5 mm ... 9.5 mm
Wire diameter	2.2 mm
Individual wire diameter	2.2 mm
Resistance to oil	yes
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	200/230 µm
Fiber type	PCF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Characteristics

Attenuation	≥ 2 dB (Insertion attenuation)
-------------	--------------------------------

Standards and regulations

Flame resistance	yes
Resistance to oil	yes
Standards/specifications	IEC PAS 61076-3-117

VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Drawings

Schematic diagram



VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1608045>



UL Listed

Approval ID: E308814-20070105

VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

VS-PPC-C1-SCRJ-MNNA-PG9-A3C-C - FO connectors



1608045

<https://www.phoenixcontact.com/us/products/1608045>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	f19f0730-faff-49ed-9cf9-80d90c48c1e1

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com