

RC-09S1N12M0K5 - Coupler connector

1596129

<https://www.phoenixcontact.com/us/products/1596129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Coupler connector, application: Signal, series: RC, straight plastic-sheathed, shielded: yes, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240683

Commercial data

Item number	1596129
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356209908
Weight per piece (including packing)	40.95 g
Weight per piece (excluding packing)	40.95 g
Country of origin	DE

RC-09S1N12M0K5 - Coupler connector



1596129

<https://www.phoenixcontact.com/us/products/1596129>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Type	Coupling housing
Thread type	M23
Design	straight plastic-sheathed
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Seal)	FPM (O-ring)

RC-09S1N12M0K5 - Coupler connector



1596129

<https://www.phoenixcontact.com/us/products/1596129>

Degree of protection (plugged in)	IP67
-----------------------------------	------

RC-09S1N12M0K5 - Coupler connector




1596129

<https://www.phoenixcontact.com/us/products/1596129>

Drawings

Schematic diagram




Connector pin assignment

RC-09S1N12M0K5 - Coupler connector

1596129

<https://www.phoenixcontact.com/us/products/1596129>

Schematic diagram



Connector pin assignment

RC-09S1N12M0K5 - Coupler connector



1596129

<https://www.phoenixcontact.com/us/products/1596129>

Schematic diagram



Dimensional drawing

RC-09S1N12M0K5 - Coupler connector



1596129

<https://www.phoenixcontact.com/us/products/1596129>

Classifications

ECLASS

ECLASS-13.0

27440116

UNSPSC

UNSPSC 21.0

39121400

RC-09S1N12M0K5 - Coupler connector



1596129

<https://www.phoenixcontact.com/us/products/1596129>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7851762e-9c6b-4601-9495-8cc4197662a9

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com