

# HC-26S1N1280NS - Cable connector



1608273

<https://www.phoenixcontact.com/us/products/1608273>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Socket, shielded: yes, degree of protection: IP67, number of positions: 26, connection method: Solder cup, series: HC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1608273
Packing unit	12 pc
Minimum order quantity	12 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJA
GTIN	4046356387040
Weight per piece (including packing)	95.3 g
Weight per piece (excluding packing)	84.189 g
Customs tariff number	85366990
Country of origin	DE

# HC-26S1N1280NS - Cable connector



1608273

<https://www.phoenixcontact.com/us/products/1608273>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

### Material specifications

Material Housing	Metal
Seal material	FPM or NBR or EPDM

### Connection data

#### Conductor connection

Connection method	Solder cup
-------------------	------------

### Electrical properties

#### Contact

Contact diameter	1 mm
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
Nominal current I <sub>N</sub>	8 A
Nominal voltage U <sub>N</sub>	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

### Connector

Type	straight
Direction of rotation	Standard

#### Connection 1

Head design	Socket
Head cable outlet	straight

# HC-26S1N1280NS - Cable connector



1608273

<https://www.phoenixcontact.com/us/products/1608273>

Head thread type	M27
------------------	-----

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# HC-26S1N1280NS - Cable connector




1608273

<https://www.phoenixcontact.com/us/products/1608273>

## Drawings

Schematic diagram



Connector pin assignment

# HC-26S1N1280NS - Cable connector



1608273

<https://www.phoenixcontact.com/us/products/1608273>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-26S1N1280NS - Cable connector



1608273

<https://www.phoenixcontact.com/us/products/1608273>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4d4e7080-163a-4896-968d-a0f02c2d3472

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)