

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert




1609565

<https://www.phoenixcontact.com/us/products/1609565>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

MSTB contact insert, for PCB assembly, 24 V, 5-pos., with straight solder pins, RAL 9005 (black), for panel mounting frame VS-PPC-F2-MSTB-...-1R-P



Commercial data

Item number	1609565
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AB17
Product key	ABNOJA
GTIN	4046356175876
Weight per piece (including packing)	2.408 g
Weight per piece (excluding packing)	2.408 g
Customs tariff number	85366990
Country of origin	DE

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert



1609565

<https://www.phoenixcontact.com/us/products/1609565>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
Notes on operation	In accordance with IEC 61984, the connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load.

Product properties

Product type	Female insert
Type	Version 14
Number of positions	5
Pitch	5.08 mm

Electrical properties

Rated voltage (III/3)	24 V
Rated current	16 A
Insulation resistance	≥ 500 MΩ
Transmission medium	Copper
Power transmission	Power

Connection data

Connection technology	
Connection method	PCB connection

Dimensions

Width	16.6 mm
Height	10.4 mm
Length	27.4 mm
Pitch	5.08 mm

Material specifications

Color	black
Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PA

Mechanical properties

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert



1609565

<https://www.phoenixcontact.com/us/products/1609565>

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
---------------------------------	------------------

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert




1609565

<https://www.phoenixcontact.com/us/products/1609565>

Drawings

Drilling plan/solder pad geometry



Drilling diagram

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert




1609565

<https://www.phoenixcontact.com/us/products/1609565>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1609565>

 cULus Recognized Approval ID: E118976-20080903				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	16 A	-	-

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert



1609565

<https://www.phoenixcontact.com/us/products/1609565>

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27460202

ETIM

ETIM 10.0	EC004746
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert



1609565

<https://www.phoenixcontact.com/us/products/1609565>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com