

# RC-12P1N1293NN - Coupler connector



1597135

<https://www.phoenixcontact.com/us/products/1597135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, application: Signal, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %). This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1597135
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356378987
Weight per piece (including packing)	74.17 g
Weight per piece (excluding packing)	72.637 g
Country of origin	DE

# RC-12P1N1293NN - Coupler connector



1597135

<https://www.phoenixcontact.com/us/products/1597135>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Thread type	M23

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	1 mm <sup>2</sup>
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
----------------------	------

# RC-12P1N1293NN - Coupler connector



1597135

<https://www.phoenixcontact.com/us/products/1597135>

## Drawings

Schematic diagram



Connector pin assignment

# RC-12P1N1293NN - Coupler connector



1597135

<https://www.phoenixcontact.com/us/products/1597135>

Schematic diagram



Dimensional drawing

# RC-12P1N1293NN - Coupler connector



1597135

<https://www.phoenixcontact.com/us/products/1597135>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-12P1N1293NN - Coupler connector



1597135

<https://www.phoenixcontact.com/us/products/1597135>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)