

RC-12S2N12YP00 - Device connector front mounting



1611016

<https://www.phoenixcontact.com/us/products/1611016>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Socket, Solder cup, Axial O-ring, coding: N

The figure shows the 9-pos. product version with standard contact chamber numbering

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1611016 |
| Packing unit | 20 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | ABRAFO |
| GTIN | 4046356265270 |
| Weight per piece (including packing) | 52.62 g |
| Weight per piece (excluding packing) | 52.62 g |
| Country of origin | DE |

1611016

<https://www.phoenixcontact.com/us/products/1611016>

Technical data

Product properties

| | |
|--------------|-----------------------------------|
| Product type | Circular connectors (device side) |
|--------------|-----------------------------------|

Connector

Insulating body

| | |
|---|---|
| Coding | N |
| Material (Insulating body) | PBT |
| Material (Contact) | CuZn |
| Material (Contact surface) | Ni/Au |
| Insertion/withdrawal cycles | 50 |
| Connection method | Solder cup |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 12 |
| Direction of rotation | Counter direction |
| Connection profile | 12 |
| Number (Contact group 1) | 12 |
| Contact diameter (Contact group 1) | 1 mm |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm ² |
| Litz wires Max. cross section (Contact group 1) | 1 mm ² |
| Rated current Contact (Contact group 1) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|-------------------------|
| Type | Feed-through header |
| Thread type | M23 |
| Design | straight |
| Type of locking | Screw locking mechanism |
| Pg screw connection | none |
| Mounting type | Front mounting (Pg13,5) |
| Assembly note | Central fastening |
| Degree of protection (plugged in) | IP67 |
| Seal for the device | Axial O-ring |

RC-12S2N12YP00 - Device connector front mounting



1611016

<https://www.phoenixcontact.com/us/products/1611016>

Drawings

Schematic diagram



Connector pin assignment

RC-12S2N12YP00 - Device connector front mounting



1611016

<https://www.phoenixcontact.com/us/products/1611016>

Schematic diagram



Dimensional drawing

RC-12S2N12YP00 - Device connector front mounting



1611016

<https://www.phoenixcontact.com/us/products/1611016>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | |
|-------------------------------------|--|
|-------------------------------------|--|

| | |
|--|----------------------------|
| | No substance above 0.1 wt% |
|--|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com