

RC-12P1N8AB1EN - Front panel feed-through



1597575

<https://www.phoenixcontact.com/us/products/1597575>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Front panel feed-through, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, Flat gasket, Panel thickness min.: 3 mm, Panel thickness max.: 7 mm, cable diameter range: 3 mm ... 10.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240855

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1597575 |
| Packing unit | 20 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB31 |
| Product key | ABRAFJ |
| GTIN | 4046356216913 |
| Weight per piece (including packing) | 74.41 g |
| Weight per piece (excluding packing) | 74.41 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

RC-12P1N8AB1EN - Front panel feed-through



1597575

<https://www.phoenixcontact.com/us/products/1597575>

Technical data

Notes

| | |
|--------------------|--|
| Order information: | Order crimp contacts Ø 1 mm separately |
|--------------------|--|

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Material specifications

| | |
|------------------|-------|
| Housing material | Metal |
|------------------|-------|

Connector

Insulating body

| | |
|---|---|
| Note | Order information: Order crimp contacts Ø 1 mm separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Connection method | Crimp connection |
| Contact switching type | Pin |
| Application | Signal |
| Number of positions | 12 |
| Direction of rotation | Standard |
| Connection profile | 12 |
| Number (Contact group 1) | 12 |
| Contact diameter (Contact group 1) | 1 mm |
| Rated current Contact (Contact group 1) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|--|
| Order information: | Order contact inserts and cable clamping/shield accessories separately |
| Type | Feed-through header |
| Thread type | M23 |
| Design | straight |
| Type of locking | Screw locking mechanism |
| Pg screw connection | none |
| Mounting type | Front mounting/square flange (4x Ø 3.2 mm) |
| Material (Housing) | Metal |
| Degree of protection (plugged in) | IP67 |
| Seal for the device | Flat gasket |

RC-12P1N8AB1EN - Front panel feed-through



1597575

<https://www.phoenixcontact.com/us/products/1597575>

Seal

| | |
|-------------------------|------------------|
| External cable diameter | 3 mm ... 10.5 mm |
| Seal material | NBR |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---------------|
| Permissible humidity (storage/transport) | 50 % ... 65 % |
|--|---------------|

RC-12P1N8AB1EN - Front panel feed-through



1597575

<https://www.phoenixcontact.com/us/products/1597575>

Drawings

Schematic diagram



Connector pin assignment

RC-12P1N8AB1EN - Front panel feed-through



1597575

<https://www.phoenixcontact.com/us/products/1597575>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
|-------------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RC-12P1N8AB1EN - Front panel feed-through



1597575

<https://www.phoenixcontact.com/us/products/1597575>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 6ee523f1-4eb4-44b8-89de-530db09867f3 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com