

# RC-19P1N220000 - Contact insert



1611453

<https://www.phoenixcontact.com/us/products/1611453>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 6-pos.  
product version

Contact insert, M23, number of positions: 16+3, contact connection type: Pin, Solder-in connection, series: NC, RC, RM, TU, UC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1611453
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFU
GTIN	4046356394390
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	7.56 g
Customs tariff number	85366990
Country of origin	DE

# RC-19P1N220000 - Contact insert



1611453

<https://www.phoenixcontact.com/us/products/1611453>

## Technical data

### Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	19
Connection profile	16+3
No. of control contacts	19
Coding	N
Thread type	M23

### Electrical properties

#### Contact: Contact group 1

Contact diameter	1.5 mm
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
Nominal current I <sub>N</sub>	10 A (for max. connection cross section)
Nominal voltage U <sub>N</sub>	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

#### Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
Nominal current I <sub>N</sub>	8 A

### Connection data

Connection method	Solder-in connection
-------------------	----------------------

### Connector

Direction of rotation	Standard
-----------------------	----------

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

# RC-19P1N220000 - Contact insert




1611453

<https://www.phoenixcontact.com/us/products/1611453>

## Drawings

Schematic diagram



Connector pin assignment

# RC-19P1N220000 - Contact insert



1611453

<https://www.phoenixcontact.com/us/products/1611453>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-19P1N220000 - Contact insert



1611453

<https://www.phoenixcontact.com/us/products/1611453>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a6b23169-62bf-4d34-88be-d85b94de013e

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)