

RC-12P2N8AC1X7 - Rear panel feed-through



1598251

<https://www.phoenixcontact.com/us/products/1598251>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Rear panel feed-through, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Pin, Crimp connection, Flat gasket, Panel thickness max.: 2.5 mm, cable diameter range: 4.5 mm ... 5.5 mm, coding: N

Commercial data

Item number	1598251
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFJ
GTIN	4046356219914
Weight per piece (including packing)	86.2 g
Weight per piece (excluding packing)	82.94 g
Country of origin	DE

RC-12P2N8AC1X7 - Rear panel feed-through



1598251

<https://www.phoenixcontact.com/us/products/1598251>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Feed-through header
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Rear mounting/square flange (4x M3)
Material (Housing)	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Flat gasket

Seal

External cable diameter	4.5 mm ... 5.5 mm
-------------------------	-------------------

RC-12P2N8AC1X7 - Rear panel feed-through



1598251

<https://www.phoenixcontact.com/us/products/1598251>

Drawings

Schematic diagram



Connector pin assignment

RC-12P2N8AC1X7 - Rear panel feed-through



1598251

<https://www.phoenixcontact.com/us/products/1598251>

Classifications

ECLASS

ECLASS-13.0	27440116
-------------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-12P2N8AC1X7 - Rear panel feed-through



1598251

<https://www.phoenixcontact.com/us/products/1598251>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d4b7cd33-cb40-4ad3-bfd2-505049ec00ec

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com