

ST-3ES1N8A0000 - Contact insert



1613312

<https://www.phoenixcontact.com/us/products/1613312>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M17, contact connection type: Socket, Crimp connection

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1613312 |
| Packing unit | 30 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Product key | ABRBET |
| GTIN | 4046356399463 |
| Weight per piece (including packing) | 2.203 g |
| Weight per piece (excluding packing) | 2.203 g |
| Country of origin | DE |

Technical data

Notes

Safety note

| | |
|--------------------|---|
| <p>Safety note</p> | <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"> • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that the protective or functional ground has been properly connected. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Operate the connector only when it is fully plugged in and interlocked. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the minimum bending radius of the cable. Lay the cable without twisting it. • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12). |
|--------------------|---|

ST-3ES1N8A0000 - Contact insert



1613312

<https://www.phoenixcontact.com/us/products/1613312>

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Number of positions | 4 |
| Coding | N |
| Thread type | M17 |

Electrical properties

Contact

| | |
|-----------------------|-------|
| Nominal voltage U_N | 630 V |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Rated surge voltage | 6 kV |

Connection data

| | |
|-------------------|------------------|
| Connection method | Crimp connection |
|-------------------|------------------|

Material specifications

| | |
|--------------------------|--------|
| Material Insulating body | PA 6.6 |
|--------------------------|--------|

Connector

| | |
|-----------------------|----------|
| Direction of rotation | Standard |
|-----------------------|----------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

ST-3ES1N8A0000 - Contact insert




1613312

<https://www.phoenixcontact.com/us/products/1613312>

Drawings

Diagram



I = current strength, ϑ = ambient temperature, 3x 25 A

ST-3ES1N8A0000 - Contact insert



1613312

<https://www.phoenixcontact.com/us/products/1613312>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com