

# RC-06P1N224300 - Device connector rear mounting



1613354

<https://www.phoenixcontact.com/us/products/1613354>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector rear mounting, application: Signal, series: RC, straight, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder-in connection, Radial O-ring, Panel thickness min.: 2.7 mm, Panel thickness max.: 3.5 mm, coding: N

The figure shows the 12-pos. product version

## Commercial data

Item number	1613354
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFR
GTIN	4046356334471
Weight per piece (including packing)	37.84 g
Weight per piece (excluding packing)	33.631 g
Country of origin	DE

1613354

<https://www.phoenixcontact.com/us/products/1613354>

## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector


#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder-in connection
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number (Contact group 1)	6
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3


#### Housing

Type	Flange housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Rear mounting/square flange (4x M3)
Material (Housing)	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Radial O-ring

Drawings



Dimensional drawing




Installation dimensions

# RC-06P1N224300 - Device connector rear mounting


1613354

<https://www.phoenixcontact.com/us/products/1613354>

Dimensional drawing



Dimensional drawing



Dimensional drawing

# RC-06P1N224300 - Device connector rear mounting


1613354

<https://www.phoenixcontact.com/us/products/1613354>



Installation dimensions

Schematic diagram




Connector pin assignment

1613354

<https://www.phoenixcontact.com/us/products/1613354>

## Drilling plan/solder pad geometry



# RC-06P1N224300 - Device connector rear mounting



1613354

<https://www.phoenixcontact.com/us/products/1613354>

## Classifications

### ECLASS

ECLASS-13.0

27440116

### ETIM

ETIM 9.0

EC002635

### UNSPSC

UNSPSC 21.0

39121400

1613354

<https://www.phoenixcontact.com/us/products/1613354>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	118fc9a2-874d-492e-bc15-e6c1625c6261

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)