

RC-12S2N8A80NY - Cable connector



1600153

<https://www.phoenixcontact.com/us/products/1600153>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, straight, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Socket, Crimp connection, cable diameter range: 7.5 mm ... 9.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1069311

The figure shows the 12-pos. product version with standard contact chamber numbering

Commercial data

Item number	1600153
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	ABRAFA
GTIN	4046356228817
Weight per piece (including packing)	72.66 g
Weight per piece (excluding packing)	68.183 g
Country of origin	DE

RC-12S2N8A80NY - Cable connector



1600153

<https://www.phoenixcontact.com/us/products/1600153>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Note	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	Metal
Degree of protection (plugged in)	IP65 IP67 IP68

Seal

External cable diameter	7.5 mm ... 9.5 mm
-------------------------	-------------------

Environmental and real-life conditions

RC-12S2N8A80NY - Cable connector



1600153

<https://www.phoenixcontact.com/us/products/1600153>

Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

RC-12S2N8A80NY - Cable connector




1600153

<https://www.phoenixcontact.com/us/products/1600153>

Drawings

Schematic diagram



Connector pin assignment

RC-12S2N8A80NY - Cable connector

1600153

<https://www.phoenixcontact.com/us/products/1600153>



Schematic diagram



Connector pin assignment

RC-12S2N8A80NY - Cable connector



1600153

<https://www.phoenixcontact.com/us/products/1600153>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-12S2N8A80NY - Cable connector



1600153

<https://www.phoenixcontact.com/us/products/1600153>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	179198e5-70d9-4178-9925-74547ff8388e

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com