

RC-16S1N127500 - Coupler connector



1600875

<https://www.phoenixcontact.com/us/products/1600875>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Coupler connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N

Commercial data

Item number	1600875
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356232241
Weight per piece (including packing)	87.63 g
Weight per piece (excluding packing)	83.05 g
Country of origin	DE

RC-16S1N127500 - Coupler connector



1600875

<https://www.phoenixcontact.com/us/products/1600875>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	16
Direction of rotation	Standard
Connection profile	16
Number (Contact group 1)	16
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	Pg9

RC-16S1N127500 - Coupler connector



1600875

<https://www.phoenixcontact.com/us/products/1600875>

Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67
	IP68

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-16S1N127500 - Coupler connector




1600875

<https://www.phoenixcontact.com/us/products/1600875>

Drawings

Schematic diagram



Connector pin assignment

RC-16S1N127500 - Coupler connector



1600875

<https://www.phoenixcontact.com/us/products/1600875>

Schematic diagram



Dimensional drawing

RC-16S1N127500 - Coupler connector



1600875

<https://www.phoenixcontact.com/us/products/1600875>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-16S1N127500 - Coupler connector



1600875

<https://www.phoenixcontact.com/us/products/1600875>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	35f9974a-1f72-49aa-8af2-ed15e72bf3e0

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com