

RC-17P1N8AK0K5 - Cable connector

1601582

<https://www.phoenixcontact.com/us/products/1601582>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Cable connector, application: Signal, series: RC, straight plastic-sheathed, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1601582 |
| Packing unit | 20 pc |
| Minimum order quantity | 1 pc |
| Product key | ABRAFA |
| GTIN | 4046356235525 |
| Weight per piece (including packing) | 38.25 g |
| Weight per piece (excluding packing) | 33.919 g |
| Country of origin | DE |

RC-17P1N8AK0K5 - Cable connector



1601582

<https://www.phoenixcontact.com/us/products/1601582>

Technical data

Notes

| | |
|--------------------|--|
| Order information: | Order crimp contacts Ø 1 mm separately |
|--------------------|--|

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Insulating body

| | |
|---|---|
| Note | Order information: Order crimp contacts Ø 1 mm separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Connection method | Crimp connection |
| Contact switching type | Pin |
| Application | Signal |
| Number of positions | 17 |
| Direction of rotation | Standard |
| Connection profile | 17 |
| Number (Contact group 1) | 17 |
| Contact diameter (Contact group 1) | 1 mm |
| Rated current Contact (Contact group 1) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|---------------------------|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | straight plastic-sheathed |
| Type of locking | Screw locking mechanism |
| Pg screw connection | none |
| Material (Housing) | GD-Zn |
| Material (Rotating parts) | CuZn |
| Degree of protection (plugged in) | IP67 |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---------------|
| Permissible humidity (storage/transport) | 50 % ... 65 % |
|--|---------------|

RC-17P1N8AK0K5 - Cable connector




1601582

<https://www.phoenixcontact.com/us/products/1601582>

Drawings

Schematic diagram



Connector pin assignment

RC-17P1N8AK0K5 - Cable connector



1601582

<https://www.phoenixcontact.com/us/products/1601582>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RC-17P1N8AK0K5 - Cable connector



1601582

<https://www.phoenixcontact.com/us/products/1601582>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com