

# RC-17S1N8AC3K5 - Rear panel feed-through



1602211

<https://www.phoenixcontact.com/us/products/1602211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Rear panel feed-through, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, Radial O-ring, Panel thickness max.: 2.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

## Commercial data

Item number	1602211
Packing unit	20 pc
Minimum order quantity	1 pc
Product key	ABRAFJ
GTIN	4046356238632
Weight per piece (including packing)	82.855 g
Weight per piece (excluding packing)	79.113 g
Country of origin	DE

# RC-17S1N8AC3K5 - Rear panel feed-through



1602211

<https://www.phoenixcontact.com/us/products/1602211>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number (Contact group 1)	17
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Order information:	Order contact inserts and cable clamping/shield accessories separately
Type	Feed-through header
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Rear mounting/square flange (4x M3)
Housing material	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Radial O-ring

## Environmental and real-life conditions

### Ambient conditions

# RC-17S1N8AC3K5 - Rear panel feed-through



1602211

<https://www.phoenixcontact.com/us/products/1602211>

Permissible humidity (storage/transport)
--

50 % ... 65 %
---------------

# RC-17S1N8AC3K5 - Rear panel feed-through



1602211

<https://www.phoenixcontact.com/us/products/1602211>

## Drawings

Schematic diagram



Connector pin assignment

# RC-17S1N8AC3K5 - Rear panel feed-through



1602211

<https://www.phoenixcontact.com/us/products/1602211>

## Classifications

### ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

### ETIM

ETIM 10.0	EC003569
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1602211

<https://www.phoenixcontact.com/us/products/1602211>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ea8074b2-edfb-4a9b-ad3b-29d1fdf2f6c2

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)