

# RC-1RS1N121L00 - Cable connector



1603164

<https://www.phoenixcontact.com/us/products/1603164>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version, with standard DIN cable gland

M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1603164
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356243896
Weight per piece (including packing)	101.7 g
Weight per piece (excluding packing)	95.836 g
Country of origin	DE

# RC-1RS1N121L00 - Cable connector



1603164

<https://www.phoenixcontact.com/us/products/1603164>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Type of the screw connection	IP68 screw
Thread type	M23

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Mechanical properties

#### Mechanical data

Type of the screw connection	IP68 screw
------------------------------	------------

### Connector

#### Insulating body

Coding	N
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
----------------------	------

# RC-1RS1N121L00 - Cable connector



1603164

<https://www.phoenixcontact.com/us/products/1603164>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-1RS1N121L00 - Cable connector



1603164

<https://www.phoenixcontact.com/us/products/1603164>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fd8add6a-5780-4a7b-aa6c-46fd70977aaf

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)