

TU-07S1N8A8UDU - Cable connector



1605926

<https://www.phoenixcontact.com/us/products/1605926>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: TU, straight, shielded: yes, Bayonet locking, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 2 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1605926 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | ABRAHA |
| GTIN | 4046356255837 |
| Weight per piece (including packing) | 141.3 g |
| Weight per piece (excluding packing) | 100.13 g |
| Country of origin | DE |

TU-07S1N8A8UDU - Cable connector



1605926

<https://www.phoenixcontact.com/us/products/1605926>

Technical data

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Insulating body

| | |
|---|---|
| Note | Order information: Order crimp contacts Ø 2 mm separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Connection method | Crimp connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 7 |
| Direction of rotation | Standard |
| Connection profile | 7 |
| Number (Contact group 1) | 7 |
| Contact diameter (Contact group 1) | 2 mm |
| Rated current Contact (Contact group 1) | 20 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|-------------------------|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | straight |
| Type of locking | Bayonet locking |
| Pg screw connection | none |
| Material (Housing) | GD-Zn |
| Material (Housing surface) | Ni |
| Material (Rotating parts) | CuZn |
| Degree of protection (plugged in) | IP67 |

Seal

| | |
|-------------------------|------------------|
| External cable diameter | 2 mm ... 14.5 mm |
| Seal material | NBR |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---------------|
| Permissible humidity (storage/transport) | 50 % ... 65 % |
|--|---------------|

TU-07S1N8A8UDU - Cable connector

1605926

<https://www.phoenixcontact.com/us/products/1605926>



Drawings

Schematic diagram



Connector pin assignment


TU-07S1N8A8UDU - Cable connector

1605926

<https://www.phoenixcontact.com/us/products/1605926>



Schematic diagram



Connector pin assignment

TU-07S1N8A8UDU - Cable connector



1605926

<https://www.phoenixcontact.com/us/products/1605926>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

TU-07S1N8A8UDU - Cable connector



1605926

<https://www.phoenixcontact.com/us/products/1605926>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 10c99066-8160-4fd7-8d3e-ac3da2318976 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com