

UC-0000000N3DU - Sleeve housing for cable connector



1606047

<https://www.phoenixcontact.com/us/products/1606047>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sleeve housing for cable connector, series: UC, angled, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, Crimp connection, shielded: yes, cable diameter range: 10 mm... 14 mm



Commercial data

Item number	1606047
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	AB31
Product key	ABRAIE
GTIN	4046356256957
Weight per piece (including packing)	182.05 g
Weight per piece (excluding packing)	182.05 g
Customs tariff number	85366990
Country of origin	DE

UC-0000000N3DU - Sleeve housing for cable connector



1606047

<https://www.phoenixcontact.com/us/products/1606047>

Technical data

Notes

Order information:	Order contact inserts separately
--------------------	----------------------------------

Product properties

Product type	Sleeve housings
Series	UC
Application	Signal
Connection profile	12
Shielded	yes
Thread type	M23

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Gasket and O-ring material	FPM

Connector

Type	angled
------	--------

Cable/line

External cable diameter	10 mm ... 14 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

UC-0000000N3DU - Sleeve housing for cable connector



1606047

<https://www.phoenixcontact.com/us/products/1606047>

Drawings

Diagram



UC-0000000N3DU - Sleeve housing for cable connector



1606047

<https://www.phoenixcontact.com/us/products/1606047>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UC-0000000N3DU - Sleeve housing for cable connector



1606047

<https://www.phoenixcontact.com/us/products/1606047>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	448a4e05-c85c-41da-b1a9-37418fe57d1c

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com