

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version

M23, Coupler connector, application: Signal, series: UC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Solder cup, cable diameter range: 11.5 mm ... 13.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1606220
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIG
GTIN	4046356258128
Weight per piece (including packing)	98.985 g
Weight per piece (excluding packing)	93.911 g
Country of origin	DE

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	11.5 mm ... 13.5 mm
Seal material	FPM

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Drawings

Schematic diagram



Connector pin assignment

UC-09P1N1290AC - Coupler connector

1606220

<https://www.phoenixcontact.com/us/products/1606220>

Schematic diagram




Connector pin assignment

UC-09P1N1290AC - Coupler connector

1606220

<https://www.phoenixcontact.com/us/products/1606220>

Schematic diagram



Connector pin assignment

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Schematic diagram




Dimensional drawing

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>



UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UC-09P1N1290AC - Coupler connector



1606220

<https://www.phoenixcontact.com/us/products/1606220>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fecf62b6-c1e0-4cab-b794-3f5224871192

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com