

# UC-17P1N8A90DU - Coupler connector



1606513

<https://www.phoenixcontact.com/us/products/1606513>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.  
product version

M23, Coupler connector, application: Signal, series: UC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 2 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1606513
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAIG
GTIN	4046356260022
Weight per piece (including packing)	96.05 g
Weight per piece (excluding packing)	90.657 g
Customs tariff number	85366990
Country of origin	DE

# UC-17P1N8A90DU - Coupler connector



1606513

<https://www.phoenixcontact.com/us/products/1606513>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number (Contact group 1)	17
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

### Environmental and real-life conditions

#### Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

# UC-17P1N8A90DU - Coupler connector



1606513

<https://www.phoenixcontact.com/us/products/1606513>

## Drawings

Schematic diagram




Connector pin assignment

# UC-17P1N8A90DU - Coupler connector

1606513

<https://www.phoenixcontact.com/us/products/1606513>

Schematic diagram



Connector pin assignment

# UC-17P1N8A90DU - Coupler connector



1606513

<https://www.phoenixcontact.com/us/products/1606513>



# UC-17P1N8A90DU - Coupler connector



1606513

<https://www.phoenixcontact.com/us/products/1606513>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UC-17P1N8A90DU - Coupler connector



1606513

<https://www.phoenixcontact.com/us/products/1606513>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	19ffd7f3-4613-4267-9b77-5b40d3384052

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)