

RF-12P2N8AWA00 - Device connector front mounting



1607260

<https://www.phoenixcontact.com/us/products/1607260>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

Device connector front mounting, application: Signal, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Pin, Axial O-ring, shielded: yes, number of positions: 12, connection method: Crimp connection, series: RF, This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1329286

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1607260 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAGL |
| GTIN | 4046356174954 |
| Weight per piece (including packing) | 35.4 g |
| Weight per piece (excluding packing) | 31.263 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

1607260

<https://www.phoenixcontact.com/us/products/1607260>

Technical data

Notes

| | |
|--------------------|----------------------------------------|
| Order information: | Order crimp contacts Ø 1 mm separately |
|--------------------|----------------------------------------|

Mounting

| | |
|---------------|--------------------------------------------|
| Mounting type | Front mounting/square flange (4x Ø 3.2 mm) |
|---------------|--------------------------------------------|

Product properties

| | |
|---------------------|-----------------------------------|
| Product type | Circular connectors (device side) |
| Series | RF |
| Application | Signal |
| Number of positions | 12 |
| Connection profile | 12 |
| Shielded | yes |
| Coding | N |
| Thread type | M23 |

Material specifications

| | |
|--------------------------|--------------|
| Material Housing | GD-Zn |
| Material Rotating parts | CuZn |
| Material Housing surface | Ni |
| Material Insulating body | PA 6.6 |
| Material Seal | FPM (O-ring) |

Electrical properties

Contact

| | |
|-----------------------|---------|
| Contact diameter | 1 mm |
| Nominal current I_N | 8 A |
| Nominal voltage U_N | 48 V AC |
| | 74 V DC |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Rated surge voltage | 1.5 kV |

Connection data

Conductor connection

| | |
|-------------------------|------------------|
| Connection method | Crimp connection |
| Contact connection type | Pin |

Connector

| | |
|-----------------------|-------------------|
| Type | straight |
| Direction of rotation | Counter direction |

1607260

<https://www.phoenixcontact.com/us/products/1607260>

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Altitude | 2000 m |

Drawings

Dimensional drawing



Installation dimensions

Dimensional drawing



Dimensional drawing

1607260

<https://www.phoenixcontact.com/us/products/1607260>

Schematic diagram



Contact chamber numbering (view of plug-in side), pin counter direction

RF-12P2N8AWA00 - Device connector front mounting



1607260

<https://www.phoenixcontact.com/us/products/1607260>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1607260>

|  cUL Recognized Approval ID: E153698-20090723 | | | | |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | 20 | - |

|  UL Recognized Approval ID: E153698-20090723 | | | | |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | 20 | - |

1607260

<https://www.phoenixcontact.com/us/products/1607260>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003569 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RF-12P2N8AWA00 - Device connector front mounting



1607260

<https://www.phoenixcontact.com/us/products/1607260>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com