

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/us/products/1608249>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Push/pull panel mounting frame, metal, version 14, including contact insert with spring-cage connection, fixed 24 V coding according to Guideline for PROFINET, for rectangular mounting cutout, with seal, without fixing screws

## Commercial data

Item number	1608249
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOJA
GTIN	4046356160049
Weight per piece (including packing)	63.4 g
Weight per piece (excluding packing)	60 g
Customs tariff number	85366990
Country of origin	DE

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/us/products/1608249>

## Technical data

### Product properties

Product type	Panel-mount frame
Type	MSTB
Number of positions	5

### Insulation characteristics

Degree of pollution	2
---------------------	---

### Electrical properties


Rated voltage (III/3)	24 V
Rated current	16 A (at 20 °C)
Transmission medium	Copper

### Connection data

#### Connection technology

Connection method	Spring-cage connection
-------------------	------------------------

### Dimensions

Dimensional drawing	
Width	36.2 mm
Height	42 mm
Length	41.9 mm

### Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Contact surface material	Au/Ni

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/us/products/1608249>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C

## Mounting

Mounting type	Front mounting
---------------	----------------

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame




1608249

<https://www.phoenixcontact.com/us/products/1608249>

## Drawings

Dimensional drawing



Mounting cutout

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame




1608249

<https://www.phoenixcontact.com/us/products/1608249>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1608249>

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	16 A	- 14	-

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/us/products/1608249>

## Classifications

### ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

### ETIM

ETIM 10.0	EC002310
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-PPC-F2-MSTB-MNNA-1R-SPSA5 - Panel-mount frame



1608249

<https://www.phoenixcontact.com/us/products/1608249>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	4c4a0bf8-ed6d-40ed-af0a-97af66398454

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)