

VS-PN-CABLE-1020/PVC-5X2,5/100 - Power cable



1609523

<https://www.phoenixcontact.com/us/products/1609523>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

PROFINET power cable, 5x 2.5 mm², stranded (7-wire), outer sheath: PVC, outside diameter 11.8 mm, RAL 7001 (silver gray), oil-resistant, cable ring: 100 m



Commercial data

Item number	1609523
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF11
Product key	AF1LDA
GTIN	4046356166881
Weight per piece (including packing)	24,070 g
Weight per piece (excluding packing)	24,070 g
Customs tariff number	85444995
Country of origin	DE

1609523

<https://www.phoenixcontact.com/us/products/1609523>

Technical data

Product properties

Product type	Data cable by the meter
Sensor type	PROFINET/power
Number of positions	5

Interfaces

Signal type/category	PROFINET/power
----------------------	----------------

Cable/line

Cable length	100 m
--------------	-------

PVC gray [PVC]

Cable weight	242 kg/km
Number of positions	5
Shielded	no
Cable type	PVC gray [PVC]
Conductor structure, voltage supply	50x 0.25 mm
AWG power supply	14
Conductor cross-section	5x 2.5 mm ²
External cable diameter	11.80 mm
Outer sheath, material	PVC
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	blue, brown, black, gray, green/yellow
Overall twist	5 cores, twisted
Insulation resistance	> 0.2 MΩ*km
Nominal voltage, cable	750 V 1000 V (Fixed, protected installation)
Test voltage	4000 V
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	15 x D
Smallest bending radius, fixed installation	48 mm
Smallest bending radius, movable installation	177 mm
Flame resistance	according to IEC 60332-1-2
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -5 °C ... 70 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
---------------------------------	--

VS-PN-CABLE-1020/PVC-5X2,5/100 - Power cable



1609523

<https://www.phoenixcontact.com/us/products/1609523>

-5 °C ... 70 °C (Cable, flexible installation)

VS-PN-CABLE-1020/PVC-5X2,5/100 - Power cable



1609523

<https://www.phoenixcontact.com/us/products/1609523>

Classifications

ECLASS

ECLASS-13.0	27060106
ECLASS-15.0	27060106

ETIM

ETIM 10.0	EC003250
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-PN-CABLE-1020/PVC-5X2,5/100 - Power cable



1609523

<https://www.phoenixcontact.com/us/products/1609523>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	44.515 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com