

# VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert




1609565

<https://www.phoenixcontact.com/us/products/1609565>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

MSTB contact insert, for PCB assembly, 24 V, 5-pos., with straight solder pins, RAL 9005 (black), for panel mounting frame VS-PPC-F2-MSTB-...-1R-P



## Commercial data

Item number	1609565
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AB17
Product key	ABNOJA
GTIN	4046356175876
Weight per piece (including packing)	2.408 g
Weight per piece (excluding packing)	2.408 g
Customs tariff number	85366990
Country of origin	DE

1609565

<https://www.phoenixcontact.com/us/products/1609565>

## Technical data

### Product properties

Product type	Female insert
Type	Version 14
Number of positions	5
Pitch	5.08 mm

### Electrical properties

Rated voltage (III/3)	24 V
Rated current	16 A
Insulation resistance	≥ 500 MΩ
Transmission medium	Copper
Power transmission	Power

### Connection data

#### Connection technology

Connection method	PCB connection
-------------------	----------------

### Dimensions

Width	16.6 mm
Height	10.4 mm
Length	27.4 mm
Pitch	5.08 mm

### Material specifications

Color	black
Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PA

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
---------------------------------	------------------

# VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert




1609565

<https://www.phoenixcontact.com/us/products/1609565>

## Drawings

Drilling plan/solder pad geometry



Drilling diagram

# VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert




1609565

<https://www.phoenixcontact.com/us/products/1609565>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1609565>

 <b>cULus Recognized</b> Approval ID: E118976-20080903				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	16 A	-	-

# VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert



1609565

<https://www.phoenixcontact.com/us/products/1609565>

## Classifications

### ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27460202

### ETIM

ETIM 10.0	EC002638
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-MSTBVA 2,5/ 5-GB-5,08-BK-A - Male insert



1609565

<https://www.phoenixcontact.com/us/products/1609565>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)