

RC-17S1Y122000 - Device connector front mounting



1611389

<https://www.phoenixcontact.com/us/products/1611389>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Device connector front mounting, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Solder cup, Flat gasket, coding: Y, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1242573

Commercial data

Item number	1611389
Packing unit	40 pc
Minimum order quantity	40 pc
Sales key	NULL
Product key	ABRAFL
GTIN	4046356394239
Weight per piece (including packing)	30.65 g
Weight per piece (excluding packing)	30.65 g
Customs tariff number	85366990
Country of origin	DE

RC-17S1Y122000 - Device connector front mounting



1611389

<https://www.phoenixcontact.com/us/products/1611389>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Coding	Y
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number (Contact group 1)	17
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	II
Degree of pollution	3

Housing

Type	Flange housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Front mounting/square flange (4x Ø 2.7 mm)
Material (Housing)	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Flat gasket

RC-17S1Y122000 - Device connector front mounting

1611389

<https://www.phoenixcontact.com/us/products/1611389>

Drawings



Installation dimensions



Installation dimensions

RC-17S1Y122000 - Device connector front mounting



1611389

<https://www.phoenixcontact.com/us/products/1611389>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1611389

<https://www.phoenixcontact.com/us/products/1611389>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c8fc15ca-5c4a-4da5-ac8d-7d76e07b2e81

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com