

# CA-17F1N8A8504S - Cable connector



1619452

<https://www.phoenixcontact.com/us/products/1619452>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.  
product version

M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 10 mm ... 14.5 mm, coding: N

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1619452       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB31          |
| Product key                          | ABRAEB        |
| GTIN                                 | 4046356823951 |
| Weight per piece (including packing) | 90.1 g        |
| Weight per piece (excluding packing) | 87.161 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# CA-17F1N8A8504S - Cable connector



1619452

<https://www.phoenixcontact.com/us/products/1619452>

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Order information: | Order 17 x 1 mm crimp contacts separately |
|--------------------|---|

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Connection 1

|             |        |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

#### Insulating body

|   |   |
|---|---|
| Note  | Order information: Order crimp contacts Ø 1 mm separately |
| Coding  | N   |
| Material (Insulating body)                      | PA 6.6  |
| Connection method                               | Crimp connection  |
| Contact switching type                          | Socket  |
| Application                                     | Signal  |
| Number of positions                             | 17  |
| Direction of rotation                           | Standard  |
| Connection profile                              | 17  |
| Number (Signal contacts)                        | 17  |
| Contact diameter (Signal contacts)              | 1 mm  |
| Litz wires Min. cross section (Signal contacts) | 0.06 mm <sup>2</sup>                                      |
| Litz wires Max. cross section (Signal contacts) | 1 mm <sup>2</sup>   |
| Rated current Contact (Signal contacts)         | 8 A (for max. connection cross section)                   |
| Rated voltage Contact (Signal contacts)         | 48 V AC<br>74 V DC  |
| Rated surge voltage                             | 1.5 kV  |
| Overvoltage category                            | III   |
| Degree of pollution                             | 3   |

#### Housing

|                                   |                         |
|-----------------------------------|-------------------------|
| Type                              | Cable connector housing |
| Thread type                       | M23                     |
| Design                            | straight                |
| Type of locking                   | SPEEDCON                |
| Pg screw connection               | none                    |
| Housing material                  | Metal                   |
| Degree of protection (plugged in) | IP67                    |

#### Seal

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
|-------------------------|-------------------|

# CA-17F1N8A8504S - Cable connector



1619452

<https://www.phoenixcontact.com/us/products/1619452>

|               |     |
|---------------|-----|
| Seal material | FPM |
|---------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

# CA-17F1N8A8504S - Cable connector




1619452

<https://www.phoenixcontact.com/us/products/1619452>


## Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), standard socket

Schematic diagram



Contact chamber numbering (view of plug-in side), standard socket

# CA-17F1N8A8504S - Cable connector



1619452

<https://www.phoenixcontact.com/us/products/1619452>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-17F1N8A8504S - Cable connector



1619452

<https://www.phoenixcontact.com/us/products/1619452>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)