

RF-16S1N8A80DU - Cable connector



1613727

<https://www.phoenixcontact.com/us/products/1613727>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, application: Feedback, signal, straight, Screw locking mechanism, M23, number of positions: 16, contact connection type: Socket, shielded: yes, cable diameter range: 5 mm ... 13.2 mm, number of positions: 16, connection method: Crimp connection, series: RF

The figure shows the 12-pos.
product version

Commercial data

Item number	1613727
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAGA
GTIN	4046356401869
Weight per piece (including packing)	99.935 g
Weight per piece (excluding packing)	94.35 g
Customs tariff number	85366990
Country of origin	DE

RF-16S1N8A80DU - Cable connector



1613727

<https://www.phoenixcontact.com/us/products/1613727>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connectors (device side)
Series	RF
Application	Feedback, signal Signal
Number of positions	16
Connection profile	16
Shielded	yes
Coding	N
Thread type	M23

Material specifications

Seal material	FPM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Electrical properties

Contact

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Crimp connection
Contact connection type	Socket

Connector

Type	straight
Direction of rotation	Standard

RF-16S1N8A80DU - Cable connector



1613727

<https://www.phoenixcontact.com/us/products/1613727>

Cable/line

External cable diameter	5 mm ... 13.2 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m

RF-16S1N8A80DU - Cable connector



1613727


<https://www.phoenixcontact.com/us/products/1613727>

Drawings

Dimensional drawing



Schematic diagram



RF-16S1N8A80DU - Cable connector



1613727

<https://www.phoenixcontact.com/us/products/1613727>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RF-16S1N8A80DU - Cable connector



1613727

<https://www.phoenixcontact.com/us/products/1613727>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5edae394-de33-493c-983e-8556aa4ae6bf

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com