

# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, application: Signal, series: UC, angled, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 13.5 mm ... 14.5 mm, coding: N



The figure shows the 12-pos.  
product version

## Commercial data

Item number	1615108
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIC
GTIN	4046356409254
Weight per piece (including packing)	180.48 g
Weight per piece (excluding packing)	167.655 g
Country of origin	DE

# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number (Contact group 1)	17
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Order information:	Order contact inserts separately
Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	Pg16
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	13.5 mm ... 14.5 mm
Seal material	FPM

## Environmental and real-life conditions

### Ambient conditions

# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

Permissible humidity (storage/transport)
--

50 % ... 65 %
---------------

# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

## Drawings

Schematic diagram



Connector pin assignment


# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

Schematic diagram




Connector pin assignment

# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>



# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UC-17P1N8ANNAD - Cable connector



1615108

<https://www.phoenixcontact.com/us/products/1615108>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6c98a5bc-64d4-4315-9760-9edf72f9ca39

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)