

RC-16S1NC20000 - Contact insert



1617776

<https://www.phoenixcontact.com/us/products/1617776>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 6-pos.
product version

Contact insert, M23, number of positions: 16, contact connection type: Socket, Solder-in connection, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1617776
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABRAFU
GTIN	4046356977166
Weight per piece (including packing)	13.62 g
Weight per piece (excluding packing)	8.464 g
Country of origin	DE

RC-16S1NC20000 - Contact insert



1617776

<https://www.phoenixcontact.com/us/products/1617776>

Technical data

Product properties

Product type	Contact insert
Application	Signal
Number of positions	16
Connection profile	16
No. of control contacts	16
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Nominal current I_N	8 A (for max. connection cross section)
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Solder-in connection
-------------------	----------------------

Connector

Direction of rotation	Standard
-----------------------	----------

RC-16S1NC20000 - Contact insert




1617776

<https://www.phoenixcontact.com/us/products/1617776>

Drawings

Dimensional drawing



Dimensional drawing


RC-16S1NC20000 - Contact insert



1617776

<https://www.phoenixcontact.com/us/products/1617776>

Schematic diagram



Connector pin assignment

RC-16S1NC20000 - Contact insert



1617776

<https://www.phoenixcontact.com/us/products/1617776>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-16S1NC20000 - Contact insert



1617776

<https://www.phoenixcontact.com/us/products/1617776>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	aa734d72-3311-4956-9008-a0162d7318e8

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com