

# RC-12S1N12C3EQ - Rear panel feed-through



1618080

<https://www.phoenixcontact.com/us/products/1618080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Rear panel feed-through, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder cup, Radial O-ring, Panel thickness max.: 2.5 mm, cable diameter range: 3 mm ... 10.5 mm, coding: N

## Commercial data

Item number	1618080
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFJ
GTIN	4055626007533
Weight per piece (including packing)	89.27 g
Weight per piece (excluding packing)	88.88 g
Country of origin	DE

# RC-12S1N12C3EQ - Rear panel feed-through



1618080

<https://www.phoenixcontact.com/us/products/1618080>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	1 mm <sup>2</sup>
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Order information:	Order contact inserts and cable clamping/shield accessories separately
Type	Feed-through header
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Mounting type	Rear mounting/square flange (4x M3)
Housing material	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Radial O-ring

#### Seal

External cable diameter	3 mm ... 10.5 mm
-------------------------	------------------

# RC-12S1N12C3EQ - Rear panel feed-through



1618080

<https://www.phoenixcontact.com/us/products/1618080>

Seal material	NBR
---------------	-----

# RC-12S1N12C3EQ - Rear panel feed-through




1618080

<https://www.phoenixcontact.com/us/products/1618080>

## Drawings

Schematic diagram



Connector pin assignment

# RC-12S1N12C3EQ - Rear panel feed-through



1618080

<https://www.phoenixcontact.com/us/products/1618080>

Schematic diagram



Dimensional drawing

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)