# SF-7ES1N8A8LB1S - Cable connector

1618208

https://www.phoenixcontact.com/us/products/1618208

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRIMP



The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

Cable connector, application: Power, SPEEDCON, M23, number of positions: 4+3+PE, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 15 mm ... 18 mm, number of positions: 8, connection method: Crimp connection

## Your advantages

- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect cable diameters of 7.5 mm ... 18 mm
- Molded designs with preassembled cables on one or both sides

## Commercial data

| | |
|---|---|
| Item number | 1618208 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB32 |
| Product key | ABRBFB |
| GTIN | 4046356584470 |
| Weight per piece (including packing) | 121.9 g |
| Weight per piece (excluding packing) | 121.752 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

# Technical data

## Notes

| | |
|---|---|
| Order information: | Order crimp contacts 4 x Ø 1 mm, 4 x Ø 2 mm separately |
| Note on application | Series SF connectors are not compatible with series M23 PRO and must not be combined. |

Safety note

| | |
|---|---|
| Safety note | • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. |

## Product properties

| | |
|---|---|
| Product type | Circular connector (cable-side) |
| Application | Power |
| Number of positions | 8 |
| Connection profile | 4+3+PE |
| Shielded | yes |
| Coding | N |
| Thread type | M23 |

## Material specifications

| | |
|---|---|
| Material Housing | Metal |
| Material Seal | FPM |

## Connection data

Conductor connection

| | |
|---|---|
| Connection method | Crimp connection |

## Electrical properties

Contact: Contact group 1

| | |
|---|---|
| Contact diameter | 2 mm |
| Nominal current $I_N$ | 30 A |
| Nominal voltage $U_N$ | 630 V |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Rated surge voltage | 6 kV |

Contact: Contact group 2

| | |
|---|---|
| Contact diameter | 1 mm |
| Min. cross section | 0 mm² |
| Nominal current $I_N$ | 9 A |
| Nominal voltage $U_N$ | 250 V |
| Overvoltage category | III |

| | |
|---|---|
| Degree of pollution | 3 |
| Rated surge voltage | 4 kV |

## Connector

Connection 1

| | |
|---|---|
| Head design | Socket |
| Head thread type | M23 |

## Cable/line

| | |
|---|---|
| External cable diameter | 15 mm ... 18 mm |


## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Altitude | 3000 m |


## Drawings

Dimensional drawing





Dimensional drawing

Schematic diagram




Connector pin assignment

Diagram




I = current strength, T = ambient temperature

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002635 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 44d34dc2-79d7-4c2d-8154-1df891793673 |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com