

# CA-06P1N126Y00 - Device connector front mounting



1619876

<https://www.phoenixcontact.com/us/products/1619876>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, application: Signal, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder connection, Axial seal, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires
- Application-specific panel mounting optionally with thread or anti-rotation protection and lock nut

## Commercial data

Item number	1619876
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEL
GTIN	4046356820905
Weight per piece (including packing)	31.8 g
Weight per piece (excluding packing)	24.664 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number (Contact group 1)	0
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	6
Contact diameter (Contact group 2)	2 mm
Litz wires Max. cross section (Contact group 2)	2.5 mm <sup>2</sup>
Rated current Contact (Contact group 2)	20 A (for max. connection cross section)

#### Housing

Order information:	If necessary, order locking nut separately
Type	Feed-through header
Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Mounting type	Front mounting (M20 x 1,5)
Assembly note	Central fastening
Material (Housing)	GD-Zn
Degree of protection (plugged in)	IP67
Seal for the device	Axial seal

### Environmental and real-life conditions

# CA-06P1N126Y00 - Device connector front mounting



1619876

<https://www.phoenixcontact.com/us/products/1619876>

## Ambient conditions

Ambient temperature (operation)

-40 °C ... 125 °C

Drawings

Schematic diagram



Connector pin assignment

# CA-06P1N126Y00 - Device connector front mounting



1619876

<https://www.phoenixcontact.com/us/products/1619876>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619876>

 <b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	48 V	10 A	14	-

 <b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	48 V	20 A	14	-

# CA-06P1N126Y00 - Device connector front mounting



1619876

<https://www.phoenixcontact.com/us/products/1619876>

## Classifications

### ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

### ETIM

ETIM 10.0	EC003569
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-06P1N126Y00 - Device connector front mounting



1619876

<https://www.phoenixcontact.com/us/products/1619876>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)