

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos. product version

M23, Coupler connector, application: Signal, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 10 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629109

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1620022 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAEG |
| GTIN | 4046356819732 |
| Weight per piece (including packing) | 93.7 g |
| Weight per piece (excluding packing) | 86.853 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Order 17 x 1 mm crimp contacts separately |
|--------------------|---|

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Connection 1

| | |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

Insulating body

| | |
|---|---|
| Note | Order information: Order crimp contacts Ø 1 mm separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Connection method | Crimp connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 17 |
| Direction of rotation | Standard |
| Connection profile | 17 |
| Number (Signal contacts) | 17 |
| Contact diameter (Signal contacts) | 1 mm |
| Litz wires Min. cross section (Signal contacts) | 0.08 mm ² |
| Litz wires Max. cross section (Signal contacts) | 1 mm ² |
| Rated current Contact (Signal contacts) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Signal contacts) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|--|
| Type | Coupling housing |
| Thread type | M23 |
| Design | straight |
| Type of locking | for standard and SPEEDCON interlock |
| Pg screw connection | none |
| Housing material | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Material for screw connection | CuZn |
| Degree of protection (plugged in) | IP67 |

Seal

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

| | |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
| Seal material | NBR |

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 % |

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

Drawings

Schematic diagram



Connector pin assignment

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1620022>

|  cUL Recognized Approval ID: E335019-20141210 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 3 A | 20 | - |

|  UL Recognized Approval ID: E335019-20141210 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 5 A | 20 | - |

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-17S1N8A9008 - Coupler connector



1620022

<https://www.phoenixcontact.com/us/products/1620022>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com