

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, application: Signal, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 6 mm ... 10 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1467146

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1620075       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB31          |
| Product key                          | ABRAEG        |
| GTIN                                 | 4046356819374 |
| Weight per piece (including packing) | 96 g          |
| Weight per piece (excluding packing) | 90.441 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

## Technical data

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Connection 1

|             |        |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

#### Insulating body

|   |                    |
|---|--------------------|
| Coding  | N                  |
| Material (Insulating body)                      | PBT                |
| Material (Contact)                              | CuZn               |
| Material (Contact surface)                      | Ni/Au              |
| Insertion/withdrawal cycles                     | 100                |
| Connection method                               | Solder connection  |
| Contact switching type                          | Socket             |
| Application                                     | Signal             |
| Number of positions                             | 12                 |
| Direction of rotation                           | Standard           |
| Connection profile                              | 12                 |
| Number (Contact group 1)                        | 0                  |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC |
| Rated surge voltage                             | 1.5 kV             |
| Overvoltage category                            | III                |
| Degree of pollution                             | 3                  |
| Number (Contact group 2)                        | 12                 |
| Contact diameter (Contact group 2)              | 1 mm               |
| Litz wires Max. cross section (Contact group 2) | 1 mm <sup>2</sup>  |
| Rated current Contact (Contact group 2)         | 8 A                |

#### Housing

|                                   |  |
|-----------------------------------|--|
| Type                              | Coupling housing   |
| Thread type                       | M23  |
| Design                            | straight   |
| Type of locking                   | for standard and SPEEDCON interlock                                  |
| Pg screw connection               | none   |
| Housing material                  | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Material for screw connection     | CuZn   |
| Degree of protection (plugged in) | IP67   |

#### Seal

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

|                         |                |
|-------------------------|----------------|
| External cable diameter | 6 mm ... 10 mm |
| Seal material           | NBR            |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

## Drawings

Schematic diagram



Connector pin assignment

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1620075>

|  <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 48 V                  | 6 A                   | 18                | -                           |

|  <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 48 V                  | 8 A                   | 18                | -                           |

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-12S1N129007 - Coupler connector



1620075

<https://www.phoenixcontact.com/us/products/1620075>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | fe632e24-9e0e-4c76-8f9c-9fd5609e7520 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)