

CA-07P1N128006 - Cable connector



1619745

<https://www.phoenixcontact.com/us/products/1619745>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 6-pos.
product version

M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 4 mm ... 6 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1340670

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1619745
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEA
GTIN	4046356821728
Weight per piece (including packing)	95.7 g
Weight per piece (excluding packing)	92.32 g
Customs tariff number	85366990
Country of origin	DE

CA-07P1N128006 - Cable connector



1619745

<https://www.phoenixcontact.com/us/products/1619745>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	7
Direction of rotation	Standard
Connection profile	7
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	7
Contact diameter (Contact group 2)	2 mm
Litz wires Max. cross section (Contact group 2)	2.5 mm ²
Rated current Contact (Contact group 2)	20 A

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	4 mm ... 6 mm
Seal material	NBR

Environmental and real-life conditions

CA-07P1N128006 - Cable connector



1619745

<https://www.phoenixcontact.com/us/products/1619745>

Ambient conditions

Ambient temperature (operation)

-40 °C ... 125 °C

CA-07P1N128006 - Cable connector

1619745

<https://www.phoenixcontact.com/us/products/1619745>

Drawings

Schematic diagram



Connector pin assignment

CA-07P1N128006 - Cable connector



1619745

<https://www.phoenixcontact.com/us/products/1619745>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619745>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	48 V	10 A	14	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	48 V	20 A	14	-

CA-07P1N128006 - Cable connector



1619745

<https://www.phoenixcontact.com/us/products/1619745>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-07P1N128006 - Cable connector



1619745

<https://www.phoenixcontact.com/us/products/1619745>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9e3d6a17-faae-471f-835b-594b447ad4b9

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com