

EV-GBM3PC-3AC32A-5,0M6,0ESOC00 - AC charging cable



1621473

<https://www.phoenixcontact.com/us/products/1621473>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CHARX connect, GB/T, cable: 5 m, straight, GB/T 20234.2, Mobile AC charging cable with Vehicle Connector and Infrastructure Plug



Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles with alternating current (AC), compatible with AC GB/T vehicle charging inlets and AC GB/T infrastructure charging sockets at charging stations

Commercial data

Item number	1621473
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	XWBAEF
GTIN	4046356933995
Weight per piece (including packing)	3,370 g
Weight per piece (excluding packing)	28 g
Country of origin	CN

EV-GBM3PC-3AC32A-5,0M6,0ESOC00 - AC charging cable



1621473

<https://www.phoenixcontact.com/us/products/1621473>

Technical data

Product properties

Product type	AC charging cable
Product family	CHARX connect
Charging standard	GB/T
Charging mode	Mode 3

Electrical properties

Charging power and current (AC charging, 3-phase)

Type of charging current	AC 3-phase
Charging current	32 A AC (3-phase)
Charging power	26.6 kW (3-phase)
Rated voltage	480 V

Cable/line

Cable length	5 m
Cable type	Class 6
Cable type	straight
Cable structure	5 x 6.0 mm ² + 1 x 0.5 mm ²
External cable diameter	17.00 mm ±0.5 mm
Outer sheath, material	TPE
Cable resistance	≤ 0.0033 Ω/m (based on a power core, at an ambient temperature of 20°C)
Bending radius	min. 255 mm (15x diameter)
Cable length	5 m
External cable diameter	17.00 mm ±0.5 mm
Cable type	Class 6
Cable resistance	≤ 0.0033 Ω/m (based on a power core, at an ambient temperature of 20°C)

Standards and regulations

Standards

Standards/regulations	GB/T 20234.2
-----------------------	--------------


EV-GBM3PC-3AC32A-5,0M6,0ESOC00 - AC charging cable

1621473

<https://www.phoenixcontact.com/us/products/1621473>


Drawings

Connection diagram



Pin assignment of the Vehicle Connector

Connection diagram




Pin assignment of Infrastructure Plug

EV-GBM3PC-3AC32A-5,0M6,0ESOC00 - AC charging cable

1621473

<https://www.phoenixcontact.com/us/products/1621473>

Schematic diagram



Operating instructions

EV-GBM3PC-3AC32A-5,0M6,0ESOC00 - AC charging cable



1621473

<https://www.phoenixcontact.com/us/products/1621473>

Classifications

UNSPSC

UNSPSC 21.0	39121522
-------------	----------

EV-GBM3PC-3AC32A-5,0M6,0ESOC00 - AC charging cable



1621473

<https://www.phoenixcontact.com/us/products/1621473>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-10 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com