

# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable



1621474

<https://www.phoenixcontact.com/us/products/1621474>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CHARX connect, GB/T, 16 A permanent, 250 V AC, cable: 5 m, black, straight, housing: black, gray, GB/T 20234.2, Mobile AC charging cable with Vehicle Connector and Infrastructure Plug



## Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles with alternating current (AC), compatible with AC GB/T vehicle charging inlets and AC GB/T infrastructure charging sockets at charging stations

## Commercial data

Item number	1621474
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	XWBAAF
GTIN	4046356934008
Weight per piece (including packing)	1,600 g
Weight per piece (excluding packing)	1,600 g
Country of origin	DE

# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable



1621474

<https://www.phoenixcontact.com/us/products/1621474>

## Technical data

### Product properties

Product type	AC charging cable
Product family	CHARX connect
Charging standard	GB/T
Charging mode	Mode 3
Label	14.1 mm x 44.8 mm (customer logo on request)
Customer variations	On request

### Electrical properties

Type of signal transmission	Pulse width modulation
Note on the connection method	Crimp connection, cannot be disconnected
Coding	680 Ω (between PE and CC)

### Charging power and current (AC charging, 1-phase)

Type of charging current	AC single-phase
Charging current	16 A AC (1-phase)
Charging power	4 kW

### Pin assignment (Power contacts)

Number	3 (L, N, PE)
Rated voltage	250 V
Rated current	16 A

### Pin assignment (Signal contacts)

Number	2 (CP, CC)
Rated voltage	30 V AC
Rated current	2 A

### Material specifications

Color (Housing)	black (9005)
Color (Handle area)	black (9005)
Color (Actuating element)	silver gray (7001)
Color (Mating face)	black (9005)
Color (Protective cap)	black (9005)
Color (Cable)	black (9005)
Material (Vehicle charging connector)	Plastic
Material (Cable outer sheath)	TPE-U
Material (Contact surface)	Silver

### Cable/line

Cable length	5 m
Cable type	Class 6
Cable type	straight

# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable



1621474

<https://www.phoenixcontact.com/us/products/1621474>

Cable structure	3 x 2.5 mm <sup>2</sup> + 1 x 0.5 mm <sup>2</sup>
External cable diameter	10.50 mm ±0.4 mm
Outer sheath, material	TPE
Cable resistance	≤ 0.0076 Ω/m (based on a power core, at an ambient temperature of 20°C)
Bending radius	min. 157.5 mm (15x diameter)
Cable length	5 m
External cable diameter	10.50 mm ±0.4 mm
Cable type	Class 6
Cable resistance	≤ 0.0076 Ω/m (based on a power core, at an ambient temperature of 20°C)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Vehicle charging inlet)	IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Infrastructure charging plug)	IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Protective cap)	IP54
Ambient temperature (operation)	-30 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m (above sea level)

## Standards and regulations

### Standards

Standards/regulations	GB/T 20234.2
-----------------------	--------------


# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable

1621474

<https://www.phoenixcontact.com/us/products/1621474>

## Drawings

Connection diagram




Pin assignment of the Vehicle Connector

# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable

1621474

<https://www.phoenixcontact.com/us/products/1621474>

## Schematic diagram



## Operating instructions

# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable



1621474

<https://www.phoenixcontact.com/us/products/1621474>

## Classifications

### UNSPSC

UNSPSC 21.0	39121522
-------------	----------

# EV-GBM3C-1AC16A-5,0M2,5ESOC00 - AC charging cable



1621474

<https://www.phoenixcontact.com/us/products/1621474>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-10 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)