M23 HYBRID_CONTACT-SAMPLE-SET - Sample set

1623252

https://www.phoenixcontact.com/us/products/1623252

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sample set consisting of 4x Ø 1.0 mm, 4x Ø 0.8 mm, 5x Ø 2.0 mm socket and pin contacts for M23 hybrid connectors. Contacts included: 1621573, 1618464, 1621577, 1621575, 1618458, 1621580

Commercial data

Item number	1623252
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB36
Product key	ABRJBA
GTIN	4055626139661
Weight per piece (including packing)	22.7 g
Weight per piece (excluding packing)	14.305 g
Customs tariff number	85389099
Country of origin	DE

Technical data

Product properties

Product type	Crimp contact
Series	SH

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Min. cross section	1 mm²
Max. cross section	2.5 mm²

Contact: Contact group 2

Contact diameter	0.8 mm
Min. cross section	0.34 mm²
Max. cross section	0.5 mm²

Contact: Contact group 3

Contact diameter	1 mm
Min. cross section	0.25 mm²
Max. cross section	1 mm²

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796

UNSPSC

UNSPSC 21.0	80141600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com