

# HC-26P1N8A90DU - Coupler connector



1623254

<https://www.phoenixcontact.com/us/products/1623254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, shielded: yes, degree of protection: IP67, cable diameter range: 2 mm ... 14.5 mm, number of positions: 26, connection method: Crimp connection, series: HC

The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

## Commercial data

Item number	1623254
Packing unit	12 pc
Minimum order quantity	12 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJG
GTIN	4055626272900
Weight per piece (including packing)	94.725 g
Weight per piece (excluding packing)	86.609 g
Customs tariff number	85366990
Country of origin	DE

# HC-26P1N8A90DU - Coupler connector



1623254

<https://www.phoenixcontact.com/us/products/1623254>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

### Material specifications

Material Housing	Metal
Seal material	NBR

### Connection data

Conductor connection	
Connection method	Crimp connection

### Electrical properties

#### Contact

Contact diameter	1 mm
Nominal current $I_N$	8 A
Nominal voltage $U_N$	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connector

Type	straight
Direction of rotation	Standard

#### Connection 1

Head design	Pin
-------------	-----

### Cable/line

External cable diameter	2 mm ... 14.5 mm
-------------------------	------------------

### Environmental and real-life conditions

# HC-26P1N8A90DU - Coupler connector



1623254

<https://www.phoenixcontact.com/us/products/1623254>

## Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# HC-26P1N8A90DU - Coupler connector




1623254

<https://www.phoenixcontact.com/us/products/1623254>

## Drawings

Dimensional drawing



Dimensional drawing


# HC-26P1N8A90DU - Coupler connector



1623254

<https://www.phoenixcontact.com/us/products/1623254>

Schematic diagram



Connector pin assignment

# HC-26P1N8A90DU - Coupler connector



1623254

<https://www.phoenixcontact.com/us/products/1623254>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-26P1N8A90DU - Coupler connector



1623254

<https://www.phoenixcontact.com/us/products/1623254>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0a3a0dfe-fa8e-4852-aa22-267fa7119b8c

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)