

HC-26P2N8A0000 - Contact insert



1623296

<https://www.phoenixcontact.com/us/products/1623296>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M27, number of positions: 26, contact connection type: Pin, Crimp connection, series: HC

Commercial data

Item number	1623296
Packing unit	100 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAJT
GTIN	4055626273242
Weight per piece (including packing)	55.55 g
Weight per piece (excluding packing)	55.55 g
Country of origin	DE

HC-26P2N8A0000 - Contact insert



1623296

<https://www.phoenixcontact.com/us/products/1623296>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Contact insert
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Coding	N
Thread type	M27

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	48 V AC
	74 V DC
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Connector

Direction of rotation	Counter direction
-----------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 125 °C
---------------------------------	-------------------

HC-26P2N8A0000 - Contact insert




1623296

<https://www.phoenixcontact.com/us/products/1623296>

Drawings

Schematic diagram



Connector pin assignment

HC-26P2N8A0000 - Contact insert



1623296

<https://www.phoenixcontact.com/us/products/1623296>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-26P2N8A0000 - Contact insert



1623296

<https://www.phoenixcontact.com/us/products/1623296>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com