

# CA-16S1N8A9006 - Coupler connector



1620127

<https://www.phoenixcontact.com/us/products/1620127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.  
product version

M23, Coupler connector, application: Signal, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 4 mm ... 6 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1620127                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AB31                           |
| Product key                          | ABRAEG                         |
| GTIN                                 | 4046356819176                  |
| Weight per piece (including packing) | 88.389 g                       |
| Weight per piece (excluding packing) | 88.388 g                       |
| Customs tariff number                | 85366990                       |
| Country of origin                    | DE                             |

# CA-16S1N8A9006 - Coupler connector



1620127

<https://www.phoenixcontact.com/us/products/1620127>

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Order information: | Order 16 x Ø 1 mm crimp contacts separately |
|--------------------|---|

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Connection 1

|             |        |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

#### Insulating body

|   |  |
|---|--|
| Note  | Order information: Order 16 x Ø 1 mm crimp contacts separately |
| Coding  | N  |
| Material (Insulating body)                      | PA 6.6   |
| Connection method                               | Crimp connection   |
| Contact switching type                          | Socket   |
| Application                                     | Signal   |
| Number of positions                             | 16   |
| Direction of rotation                           | Standard   |
| Connection profile                              | 16   |
| Number (Signal contacts)                        | 16   |
| Contact diameter (Signal contacts)              | 1 mm   |
| Litz wires Min. cross section (Signal contacts) | 0.08 mm <sup>2</sup>   |
| Litz wires Max. cross section (Signal contacts) | 1 mm <sup>2</sup>  |
| Rated current Contact (Signal contacts)         | 8 A (for max. connection cross section)                        |
| Rated voltage Contact (Signal contacts)         | 48 V AC<br>74 V DC   |
| Rated surge voltage                             | 1.5 kV   |
| Overvoltage category                            | III  |
| Degree of pollution                             | 3  |

#### Housing

|                                   |  |
|-----------------------------------|--|
| Type                              | Coupling housing   |
| Thread type                       | M23  |
| Design                            | straight   |
| Type of locking                   | for standard and SPEEDCON interlock                                  |
| Pg screw connection               | none   |
| Housing material                  | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Material for screw connection     | CuZn   |
| Degree of protection (plugged in) | IP67   |

#### Seal

# CA-16S1N8A9006 - Coupler connector



1620127

<https://www.phoenixcontact.com/us/products/1620127>

|                         |               |
|-------------------------|---------------|
| External cable diameter | 4 mm ... 6 mm |
| Seal material           | NBR           |

## Environmental and real-life conditions

### Ambient conditions

|  |                   |
|--|-------------------|
| Ambient temperature (operation)          | -40 °C ... 125 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 %     |

# CA-16S1N8A9006 - Coupler connector



1620127

<https://www.phoenixcontact.com/us/products/1620127>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1620127>

|  <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 48 V                  | 3 A                   | 20                | -                           |

|  <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 48 V                  | 5 A                   | 20                | -                           |

# CA-16S1N8A9006 - Coupler connector



1620127

<https://www.phoenixcontact.com/us/products/1620127>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-16S1N8A9006 - Coupler connector



1620127

<https://www.phoenixcontact.com/us/products/1620127>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)