

CA-1RP1N8A0000 - Contact insert



1623627

<https://www.phoenixcontact.com/us/products/1623627>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 16+2+FE, contact connection type: Pin, Crimp connection, series: CA, RC

Commercial data

Item number	1623627
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB31
Product key	ABRAET
GTIN	4055626170596
Weight per piece (including packing)	2.61 g
Weight per piece (excluding packing)	2.167 g
Customs tariff number	85472000
Country of origin	DE

CA-1RP1N8A0000 - Contact insert



1623627

<https://www.phoenixcontact.com/us/products/1623627>

Technical data

Notes

Order information:	Order crimp contacts 16x Ø 1 mm, 2x Ø 1.5 mm, 1x Ø 1.5 mm (FE, first) separately
--------------------	--

Product properties

Product type	Contact insert
Series	CA RC
Application	Signal
Number of positions	19
Connection profile	16+2+FE
No. of control contacts	19
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1.5 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	10 A (for max. connection cross section)
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

CA-1RP1N8A0000 - Contact insert



1623627

<https://www.phoenixcontact.com/us/products/1623627>

Material Insulating body	PA 6.6
Flammability rating according to UL 94	V0

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m


CA-1RP1N8A0000 - Contact insert

1623627

<https://www.phoenixcontact.com/us/products/1623627>

Drawings

Schematic diagram



Connector pin assignment

CA-1RP1N8A0000 - Contact insert



1623627

<https://www.phoenixcontact.com/us/products/1623627>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-1RP1N8A0000 - Contact insert



1623627

<https://www.phoenixcontact.com/us/products/1623627>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com