

# CA-1RP1N8A80DNS - Cable connector



1623837

<https://www.phoenixcontact.com/us/products/1623837>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 16+2+FE, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N

Similar to figure, please order crimp contacts separately

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1623837                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AB31                           |
| Product key                          | ABRAEB                         |
| GTIN                                 | 4055626228402                  |
| Weight per piece (including packing) | 90.6 g                         |
| Weight per piece (excluding packing) | 87.76 g                        |
| Customs tariff number                | 85366990                       |
| Country of origin                    | DE                             |

1623837

<https://www.phoenixcontact.com/us/products/1623837>

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Order information: | Order crimp contacts 16 x Ø 1 mm, 2 x Ø 1.5 mm, 1 x Ø 1.5 (PE) separately                                     |
| Order information: | When using a specific cable with Ø 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786601) |

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|   |   |
|---|---|
| Note  | Order information: Order crimp contacts 16x Ø 1 mm, 2x Ø 1.5 mm, 1x Ø 1.5 mm (FE, first) separately |
| Coding  | N   |
| Material (Insulating body)                      | PA 6.6  |
| Flammability rating according to UL 94          | V0  |
| Insertion/withdrawal cycles                     | 100   |
| Connection method                               | Crimp connection  |
| Contact switching type                          | Pin   |
| Application                                     | Signal  |
| Number of positions                             | 19  |
| Direction of rotation                           | Standard  |
| Connection profile                              | 16+2+FE   |
| Installation height                             | 2000 m  |
| Number (Contact group 1)                        | 3   |
| Contact diameter (Contact group 1)              | 1.5 mm  |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>  |
| Litz wires Max. cross section (Contact group 1) | 1 mm <sup>2</sup>   |
| Rated current Contact (Contact group 1)         | 10 A (for max. connection cross section)  |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC  |
| Rated surge voltage                             | 1.5 kV  |
| Overvoltage category                            | II  |
| Degree of pollution                             | 3   |
| Number (Contact group 2)                        | 16  |
| Contact diameter (Contact group 2)              | 1 mm  |
| Litz wires Max. cross section (Contact group 2) | 1 mm <sup>2</sup>   |
| Rated current Contact (Contact group 2)         | 8 A   |
| Rated voltage Contact (Contact group 2)         | 48 V AC<br>48 V AC  |
| Rated surge voltage                             | 1.5 kV  |
| Overvoltage category                            | III   |

# CA-1RP1N8A80DNS - Cable connector



1623837

<https://www.phoenixcontact.com/us/products/1623837>

|                     |   |
|---------------------|---|
| Degree of pollution | 3 |
|---------------------|---|

## Housing


|                                   |                         |
|-----------------------------------|-------------------------|
| Type                              | Cable connector housing |
| Thread type                       | M23                     |
| Design                            | straight                |
| Type of locking                   | SPEEDCON                |
| Pg screw connection               | none                    |
| Housing material                  | CuZn, GD-Zn             |
| Degree of protection (plugged in) | IP67                    |

## Seal

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 3 mm ... 14.5 mm |
| Seal material           | NBR              |

Drawings

Schematic diagram



Connector pin assignment

Schematic diagram



Connector pin assignment

# CA-1RP1N8A80DNS - Cable connector



1623837

<https://www.phoenixcontact.com/us/products/1623837>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-1RP1N8A80DNS - Cable connector



1623837

<https://www.phoenixcontact.com/us/products/1623837>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)