

TU-63P1N12TUDU - Cable connector



1624723

<https://www.phoenixcontact.com/us/products/1624723>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: TU, angled, shielded: yes, Bayonet locking, No. of pos.: 6+3, Direction of rotation: Standard, contact connection type: Pin, Solder cup, cable diameter range: 2 mm ... 14.5 mm, coding: N

Commercial data

Item number	1624723
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAHC
GTIN	4046356622240
Weight per piece (including packing)	141.72 g
Weight per piece (excluding packing)	141.72 g
Country of origin	DE

TU-63P1N12TUDU - Cable connector



1624723

<https://www.phoenixcontact.com/us/products/1624723>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	6+3
Number (Contact group 1)	3
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	6
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A

Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Bayonet locking
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)

TU-63P1N12TUDU - Cable connector



1624723

<https://www.phoenixcontact.com/us/products/1624723>

Degree of protection (plugged in)	IP67
Seal	
External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

TU-63P1N12TUDU - Cable connector




1624723

<https://www.phoenixcontact.com/us/products/1624723>

Drawings

Schematic diagram



Connector pin assignment

TU-63P1N12TUDU - Cable connector



1624723

<https://www.phoenixcontact.com/us/products/1624723>

Schematic diagram




Dimensional drawing

TU-63P1N12TUDU - Cable connector



1624723

<https://www.phoenixcontact.com/us/products/1624723>



TU-63P1N12TUDU - Cable connector



1624723

<https://www.phoenixcontact.com/us/products/1624723>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com